



Technical Tapes – Cloth Tape

HelaTape Tex

Features and benefits

- High quality PE-coated cloth tape with good weather resistance
- Total thickness of 0.31 mm for high tensile strength
- Highly tear-resistant in longitudinal direction
- Easy to tear-off by hand in transverse direction
- Matt surface finish for use in stage constructions and for exhibitions to avoid light reflections
- Useful for various applications like bundling, fixing, identification, marking and protection
- HelaTape Tex can be removed without residues due to high quality rubber based adhesive



HelaTape Tex is available in various colours and sizes.

MATERIAL	Cotton (CO)
Operating Temperature	-30 °C to +80 °C
Adhesion to Backing	3 N/10 mm
Elongation at break	10 %
Breaking Strength	64 N/10 mm

HF

RoHS

TYPE	Thickness (T)	Width (W)	Length (L)	Colour	Article-No.
HTAPE-TEX-19x10	0.31	19.0	10.0 m	Black (BK)	712-00204
	0.31	19.0	10.0 m	Blue (BU)	712-00200
	0.31	19.0	10.0 m	Green (GN)	712-00203
	0.31	19.0	10.0 m	Grey (GY)	712-00206
	0.31	19.0	10.0 m	Red (RD)	712-00201
	0.31	19.0	10.0 m	White (WH)	712-00205
	0.31	19.0	10.0 m	Yellow (YE)	712-00202
HTAPE-TEX-19x50	0.31	19.0	50.0 m	Black (BK)	712-00504
	0.31	19.0	50.0 m	Blue (BU)	712-00500
	0.31	19.0	50.0 m	Green (GN)	712-00503
	0.31	19.0	50.0 m	Grey (GY)	712-00506
	0.31	19.0	50.0 m	Red (RD)	712-00501
	0.31	19.0	50.0 m	White (WH)	712-00505
	0.31	19.0	50.0 m	Yellow (YE)	712-00502
HTAPE-TEX-50x50	0.31	50.0	50.0 m	Black (BK)	712-00904
	0.31	50.0	50.0 m	Blue (BU)	712-00900
	0.31	50.0	50.0 m	Green (GN)	712-00903
	0.31	50.0	50.0 m	Grey (GY)	712-00906
	0.31	50.0	50.0 m	Red (RD)	712-00901
	0.31	50.0	50.0 m	White (WH)	712-00905
	0.31	50.0	50.0 m	Yellow (YE)	712-00902

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.