
**Part Number :** 5601230802
**Product Description :** DuraClik ISL Wire-to-Board Receptacle Housing, Single Row, Red, 8 Circuits
**Series Number :** 560123
**Status :** Active
**Product Category :** Connector Housings



## Documents and Resources

### Drawings

5601230802_sd.pdf

### 3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

### Specifications

AS-560123-001-001.pdf

PK-560123-001-001.pdf

PS-560123-001-001.pdf (Tin Plating)

PS-560123-003-001.pdf (Tin Plating)

5601240131-000.pdf (Gold Plating)

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Compliant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Compliant per 2000/53/EC |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Downloaded from Arrow.com.

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Connector Housings |
| Series | 560123 |
| Description | DuraClik ISL Wire-to-Board Receptacle Housing, Single Row, Red, 8 Circuits |
| Application | Automotive, Wire-to-Board |
| Component Type | Housing |
| Product Name | DuraClik |
| UPC | 889056617185 |

### Agency

| | |
|---|---|
| UL | E29179 |

### Physical

| | |
|---|---|
| Circuits (maximum) | 8 |
| Color - Resin | Red |
| Gender | Receptacle |
| Glow-Wire Capable | No |
| Keying to Mating Part | No |

Downloaded from Arrow.com.

| | |
|---|---|
| Lock to Mating Part | Yes |
| Material - Resin | Polybutylene Terephthalate (PBT) |
| Net Weight | 0.455/g |
| Number of Rows | 1 |
| Packaging Type | Bag |
| Panel Mount | No |
| Pitch - Mating Interface | 2.00mm |
| Pitch - Termination Interface | 2.00mm |
| Polarized to Mating Part | Yes |
| Stackable | No |
| Temperature Range - Operating | -40° to +130°C |

## Mates With / Use With

### Mates with Part(s)

| Description | Part Number |
|---|---|
| DuraClik Right-Angle Single Row Headers | 502352 |
| DuraClik Vertical Single Row Headers | 560020 |

### Use with Part(s)

| Description | Part Number |
|---|---|
| DuraClik Wire-to-Board Independent Secondary Lock (ISL) Retainer, 8 Circuits, Gray | 5601250800 |
| DuraClik ISL Female Crimp Terminals | 560124 |



Downloaded from Arrow.com.