



Part Number : [732162160](#)

Product Description : TNC Jack, Straight, Bulkhead, Isolated Ground, Crimp, RG-178 Cable, Brass Body, Nickel (Ni) Plated, 50 Ohms

Series Number : 73216

Status : Active

Product Category : RF / Coaxial Connectors



Documents & Resources

Drawings

[732162160 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2021)4569-DC (8 July 2021)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73216
Description	TNC Jack, Straight, Bulkhead, Isolated Ground, Crimp, RG-178 Cable, Brass Body, Nickel (Ni) Plated, 50 Ohms
Application	RF
Product Name	TNC
Style	Cable
Type	Miniature
UPC	883906924836

Electrical

Frequency	11 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 500 Vrms@Sea Level

Physical

Cable Attachment	Crimp
Gender	Jack
Keying to Mating Part	N/A
Net Weight	15.124/g
Orientation	Straight
Packaging Type	Bag

Panel Mount	Yes
Panel Mount Method	Bulkhead
PCB Mounting	N/A
PCB Thickness - Recommended	3.94mm
Reverse Polar	No
Wire/Cable Type	RG-178, RG-196

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

This document was generated on Sep 16, 2025