

Part Number : 690081090
Product Description : PremiumGrade Hand Crimp Tool for Picoflex PF-50 IDT Receptacle, 4-26 Circuits, 28-26 AWG Flat Cable, 1.00mm max. Thickness
Series Number : 207129
Status : Active
Product Category : Crimp Presses and Crimp Hand Tools

Documents and Resources

Tooling Specifications

ATS-690081090-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Downloaded from Arrow.com.

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Presses and Crimp Hand Tools
Series	207129
Description	PremiumGrade Hand Crimp Tool for Picoflex PF-50 IDT Receptacle, 4-26 Circuits, 28-26 AWG Flat Cable, 1.00mm max. Thickness
Comments	690081093 Insertion Blade
Function	Insulation Displacement (IDT)
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	N/A
Tool Type	Hand Crimp Tool
UPC	822348441877
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Downloaded from Arrow.com.

Applicable Parts

Description	Part Number
Picoflex PF-50, Low Profile, IDT Receptacle, 4 Circuits, White, Tin (Sn) Plated, Bag	903270304
Picoflex PF-50, Low Profile, IDT Receptacle, 6 Circuits, White, Tin (Sn) Plated, Bag	903270306
Picoflex PF-50, Low Profile, IDT Receptacle, 8 Circuits, White, Tin (Sn) Plated, Bag	903270308
Picoflex PF-50, Low Profile, IDT Receptacle, 10 Circuits, White, Tin (Sn) Plated, Bag	903270310
Picoflex PF-50, Low Profile, IDT Receptacle, 12 Circuits, White, Tin (Sn) Plated, Bag	903270312
Picoflex PF-50, Low Profile, IDT Receptacle, 14 Circuits, White, Tin (Sn) Plated, Bag	903270314
Picoflex PF-50, Low Profile, IDT Receptacle, 16 Circuits, White, Tin (Sn) Plated, Bag	903270316
Picoflex PF-50, Low Profile, IDT Receptacle, 18 Circuits, White, Tin (Sn) Plated, Bag	903270318
Picoflex PF-50, Low Profile, IDT Receptacle, 20 Circuits, White, Tin (Sn) Plated, Bag	903270320
Picoflex PF-50, Low Profile, IDT Receptacle, 22 Circuits, White, Tin (Sn) Plated, Bag	903270322
Picoflex PF-50, Low Profile, IDT Receptacle, 24 Circuits, White, Tin (Sn) Plated, Bag	903270324
Picoflex PF-50, Low Profile, IDT Receptacle, 26 Circuits, White, Tin (Sn) Plated, Bag	903270326
Picoflex PF-50, Low Profile, IDT Receptacle, 4 Circuits, White, Gold (Au) Plated, Bag	903273304

Downloaded from Arrow.com.

Picoflex PF-50, Low Profile, IDT Receptacle, 6 Circuits, White, Gold (Au) Plated, Bag	903273306
Picoflex PF-50, Low Profile, IDT Receptacle, 8 Circuits, White, Gold (Au) Plated, Bag	903273308
Picoflex PF-50, Low Profile, IDT Receptacle, 10 Circuits, White, Gold (Au) Plated, Bag	903273310
Picoflex PF-50, Low Profile, IDT Receptacle, 12 Circuits, White, Gold (Au) Plated, Bag	903273312
Picoflex PF-50, Low Profile, IDT Receptacle, 14 Circuits, White, Gold (Au) Plated, Bag	903273314
Picoflex PF-50, Low Profile, IDT Receptacle, 16 Circuits, White, Gold (Au) Plated, Bag	903273316
Picoflex PF-50, Low Profile, IDT Receptacle, 18 Circuits, White, Gold (Au) Plated, Bag	903273318
Picoflex PF-50, Low Profile, IDT Receptacle, 20 Circuits, White, Gold (Au) Plated, Bag	903273320
Picoflex PF-50, Low Profile, IDT Receptacle, 22 Circuits, White, Gold (Au) Plated, Bag	903273322
Picoflex PF-50, Low Profile, IDT Receptacle, 24 Circuits, White, Gold (Au) Plated, Bag	903273324
Picoflex PF-50, Low Profile, IDT Receptacle, 26 Circuits, White, Gold (Au) Plated, Bag	903273326
1.27mm Pitch Picoflex PF-50 IDT Receptacle, Low Profile, Board-in, 4 Circuits	905841304
1.27mm Pitch Picoflex PF-50 IDT Receptacle, Low Profile, Board-in, 6 Circuits	905841306
1.27mm Pitch Picoflex PF-50 IDT Receptacle, Low Profile, Board-in, 8 Circuits	905841308

Downloaded from Arrow.com.

1.27mm Pitch Picoflex PF-50 IDT Receptacle, Low Profile, Board-in, 10 Circuits	905841310
1.27mm Pitch Picoflex PF-50 IDT Receptacle, Low Profile, Board-in, 12 Circuits	905841312
1.27mm Pitch Picoflex PF-50 IDT Receptacle, Low Profile, Board-in, 14 Circuits	905841314
1.27mm Pitch Picoflex PF-50 IDT Receptacle, Low Profile, Board-in, 16 Circuits	905841316
1.27mm Pitch Picoflex PF-50 IDT Receptacle, Low Profile, Board-in, 18 Circuits	905841318
1.27mm Pitch Picoflex PF-50 IDT Receptacle, Low Profile, Board-in, 20 Circuits	905841320
1.27mm Pitch Picoflex PF-50 IDT Receptacle, Low Profile, Board-in, 22 Circuits	905841322
1.27mm Pitch Picoflex PF-50 IDT Receptacle, Low Profile, Board-in, 24 Circuits	905841324
1.27mm Pitch Picoflex PF-50 IDT Receptacle, Low Profile, Board-in, 26 Circuits	905841326

Downloaded from Arrow.com.