



REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
A1	-	RELEASE NEW DRAWING	11APR18	ROOKIE	TOMMY


P/N AT04-12PA-P075
KEY-A CONFIGURATION
STANDARD COLOR: GREY




P/N AT04-12PB-P075
KEY-B CONFIGURATION
STANDARD COLOR: BLACK



P/N AT04-12PC-P075
KEY-C CONFIGURATION
STANDARD COLOR: GREEN



P/N AT04-12PD-P075
KEY-D CONFIGURATION
STANDARD COLOR: BROWN



PART NUMBER		DESCRIPTION		ITEM
QUANTITY		MATERIALS LIST		
UNLESS OTHERWISE SPECIFIED 1) All dimensions are in metric(mm). 2) Tolerances are as follows: 1 PL DEC ±0.30 2 PL DEC ±0.15 3 PL DEC ±0.08 3) Note reference = 		SIGNATURES DRAWN: ROOKIE CHECKED: ORION ENGINEER: APPROVAL: TOMMY CUSTOMER:	DATE 11APR18 11APR18 11APR18	Amphenol Sine Systems - www.amphenol-sine.com 44724 Morley Drive Clinton Township, MI 48036 AT 12WAY RECEPTACLE (3)4 PIN BUSBAR-NICKEL PLATED
MATERIAL SPECIFICATIONS:		THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.		
PROCESS SPECIFICATIONS:		SIZE: B C- DWG NO: AT04-12PX-P075 REVISION: A1		
NEXT ASSY:		SCALE: NONE SHEET 2 OF 2		

TITLE: AT 12WAY RECEPTACLE (3)4 PIN BUSBAR-NICKEL PLATED
DWG NO: AT04-12PX-P075
REV: A1
SH: 2
OF: 2