



PART FINDER

FIND NOW

Find faster what you're looking for!

Product Overview

Connectors

Customer specific solutions

Pin and female header

LED connectors

USB 3.1 Typ C & USB 3.0

USB

IEEE 1394

Modular

Terminal Blocks

D SUB

D SUB cover

D SUB accessories

DIN41651 (IDC)

FFC / FPC connectors

Micro-Miniature

DVI

Centronics

Power supply

DIN 41612

DIN 41617

Mini DIN

IC Socket

Jumper

Connector sleeves

Solder terminals

Test terminals

Memory Card connectors

Keystone Jack

Gender Changer

Modular Plug

Waterproof parts

Thermal management

Cable assembly

Capabilities

IT Network Products



download
technical drawing



download
Product Change Notification



3D view

Pin and female header

AW 109/02-T Pin-&female-header pin header THT single row 2,54mm 2pin straight stamped contacts gold plated polybag

Part number: AW 109/02-T

product group: Pin-&female-header

style: pin header

contact type: THT

pin count: 2

spacing in mm: 2.54

current rating: 1,5A

version: single row

total length: 11.2mm

length mating side: 6.7mm

length solder side: 3.0mm

contact direction: straight

plating: gold plated

contact machining: stamped contacts

packaging: polybag

insulator: PBT UL94V-0

10- years employment jubilee

Management honors employees for their 10- years jubilee with the ASSMANN WSW AWARD



MORE NEWS 



Company Film

Watch our company video!

[START WATCHING](#)

Contact

1840 W. Drake Drive, Suite 101
Tempe AZ, 85283, USA
+1 (480) 8977 001
info@assmann-wsw-usa.com

[TO CONTACT](#)



 PART FINDER

 IMPRINT

 SITEMAP

 TERMS & CONDITIONS

 PRIVACY POLICY

 PRINT

 RECOMMEND