

Finisar®

Active Optical Cables



Active Optical Cables for High-Performance Connectivity

Finisar’s family of active optical cables accelerate data connectivity for storage, networking and high-performance computing (HPC) applications. This product line includes C.wire® for 100GbE and InfiniBand 12xQDR/12xFDR/4xEDR; Quadwire® for 40/100GbE and InfiniBand 4xQDR/4xFDR/4xEDR; and SFPwire™ for applications up to 10 Gb/s.

Each cable solution leverages Finisar’s fiber optic technology for the transmission of data while reducing the weight, density and power consumption of traditional copper solutions. Key advantages of active optical cables include low weight for high port count architectures; small bend radius for easy installations; and low power consumption enabling a greener environment thereby providing the lowest total cost solution for data centers.



12-Channel Parallel Active Optical Cables for 100GbE and InfiniBand 12xQDR/12xFDR

C.wire® is a family of 12-channel parallel active optical cables that enables high-speed data connectivity for storage, networking, and high-performance computing (HPC) applications. It supports up to 12x14 Gb/s bi-directionally over parallel multimode fiber (MMF) cable. Based on Finisar’s vertically integrated VCSEL array technology and designed with CXP-compliant high-density connectors, these cables are compact, lightweight, and low power. C.wire is well suited for data center reaches up to 300 meters for InfiniBand 12xQDR/12xFDR, 100G Ethernet, PCIe, and other proprietary datacom and HPC applications. C.wire is available in a point-to-point configuration using MSA compliant CXP modules on each end, as well as a fanout configuration with a CXP module on one end and three separate QSFP+ modules at the other end.



Product Selection

Part No: FCBRD10CD1Cxx		
12x10 Gb/s CXP-CXP active optical cable, round, riser-rated		
Part No: FCBND10CD1Cxx		
12x10 Gb/s CXP-CXP active optical cable, round, plenum-rated		
Part No: FCBR3Q02CxxC1		
12x10Gb/s CXP-3xQSFP+ fanout active optical cable, round/flat, riser-rated		
Part No: FCBN3Q02CxxC1		
12x10Gb/s CXP-3xQSFP+ fanout active optical cable, round, plenum-rated		
Part No: FCBRD12CD1Cxx		
12x12.5 Gb/s CXP-CXP active optical cable, round, riser-rated		
Part No: FCBND12CD1Cxx		
12x12.5 Gb/s CXP-CXP active optical cable, round, plenum-rated		
Part No: FCBRD14CD1Cxx		
12x14 Gb/s CXP-CXP active optical cable, round, riser-rated		
Part No: FCBND14CD1Cxx		
12x14 Gb/s CXP-CXP active optical cable, round, plenum-rated		
xx	03	3 meter cable
	05	5 meter cable
	10	10 meter cable
	20	20 meter cable
	30	30 meter cable
	50	50 meter cable
	X0	100 meter cable



4-Channel Parallel Active Optical Cable for InfiniBand 4xQDR/4xFDR, Ethernet 40 GbE, Fibre Channel, SAS 2/3, and PCIe 2/3

Quadwire® is a family of 4-channel parallel active optical cables that facilitates high-speed data connectivity for storage, networking, and high-performance computing (HPC) applications. It supports up to 4x25Gb/s bi-directional connectivity using parallel multimode fiber (MMF) cables. Based on Finisar's vertically integrated VCSEL array technology, these cables are compact, lightweight, and low power. Quadwire is ideally suited for data center reaches up to 100 meters for InfiniBand QDR/FDR/EDR, 40/100G Ethernet, SAS, PCIe, and other datacom and HPC applications. Quadwire is available in a point-to-point configuration using MSA compliant QSFP+ modules on each end, as well as a fanout configuration with a QSFP+ module on one end and four separate SFP+ modules at the other ends.



Product Selection

Part No: FCBG410QB1Cxx		
4x10Gb/s QSFP-QSFP active optical cable, LSZH, flat ribbon, riser-rated		
Part No: FCBN410QB1Cxx		
4x10Gb/s QSFP-QSFP active optical cable, round, plenum-rated		
Part No: FCBN510E2Cxx		
4x10Gb/s QSFP-4xSFP+ fanout active optical cable, round, plenum-rated		
Part No: FCBG414QB1Cxx		
4x14Gb/s QSFP-QSFP active optical cable, LSZH, flat ribbon, riser-rated		
Part No: FCBN414QB1Cxx		
4x14Gb/s QSFP-QSFP active optical cable, round, plenum-rated		
Part No: FCBN425QB1Cxx		
4x25Gb/s QSFP-QSFP active optical cable, round, plenum-rated		
xx	03	3 meter cable
	05	5 meter cable
	10	10 meter cable
	15	15 meter cable
	20	20 meter cable
	30	30 meter cable
	50	50 meter cable
	X0	100 meter cable



10 Gb/s SFP+ Active Optical Cable for 10G Ethernet

SFPwire™ is a family of 10G active optical cables for high-speed data links between SFP+ ports. SFPwire is ideally suited for inter-rack and intra-rack connections within a data center environment. Based on Finisar's vertically integrated VCSEL array technology and designed with SFP+ SFI-limiting module ends, SFPwire is lighter and more flexible than comparable copper SFP+ direct attach cables (DACs).

Product Selection

Part No: FCBG110SD1Cxx		
xx	01	1 meter cable
	03	3 meter cable
	05	5 meter cable
	07	7 meter cable
	10	10 meter cable
	20	20 meter Scable



::::C.wire®

::quadwire®

SFP⁺wire™

www.finisar.com/cables
phone: +1-408-548-1000
sales: +1-408-541-5690
email: cables@finisar.com



Scan this code to access the website

Finisar®

1389 Moffett Park Drive
Sunnyvale, CA 94089-1133

Telephone: +1-408-548-1000
Sales: +1-408-541-5690
www.finisar.com

©2014 Finisar Corporation. All rights reserved. Finisar, Quadwire, and C.wire are registered trademarks and SFPwire is a trademark of Finisar Corporation. Features and specifications are subject to change without notice. 04/14