



Pushing Performance
Since 1945

PPV4 2.0 Signal 20p d.e. 20x0,14qmm 1,0m



Image is for illustration purposes only. Please refer to product description.

Part number	09 48 353 5848 010
Specification	PPV4 2.0 Signal 20p d.e. 20x0,14qmm 1,0m
HARTING eCatalogue	https://harting.com/09483535848010

Identification

Category	System cabling
Series	HARTING PushPull (V4)
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	HARTING PushPull (V4) Signal 20 poles
Connector 2	HARTING PushPull (V4) Signal 20 poles
Type of cable	Copper cable (round)
Description of the cable	Wiring 1:1

Version

Cable length	1 m
Number of cores	20
Core structure	20x AWG 26/7
Shielding	Shielded

Technical characteristics

Contact spacing (termination side)	1.9 mm 2 mm
Contact spacing (mating side)	1.9 mm 2 mm
Rated current	2 A
Rated voltage	50 V



Pushing Performance
Since 1945

Technical characteristics

Clearance distance	≥1.2 mm
Creepage distance	≥1.9 mm
Insulation resistance	>10 ⁸ Ω
Contact resistance	≤20 mΩ
Limiting temperature	-40 ... +80 °C
Insertion force	50 N
Withdrawal force	50 N
Mating cycles	≥100
Test voltage U _{r.m.s.}	2 kV (contact-contact) 2 kV (contact-ground)
Isolation group	I (600 ≤ CTI)
Vibration resistance	10-500 Hz, 5 g, 0.35 mm, 10 sweep cycles acc. to IEC 61373 Category 1 Class B
Shock resistance	50 g / 11 ms, 3 shocks / axis and direction

Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	Black
Material (contacts)	Copper alloy
Surface (contacts)	Silver plated Termination side Silver plated Mating side
Material (cable)	PUR (polyurethane)
Colour (cable)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel



Pushing Performance
Since 1945

Specifications and approvals

Specifications	IEC 61076-3-106 Variant 4 (V4)
----------------	--------------------------------

Commercial data

Packaging size	1
Net weight	1 g
Country of origin	Latvia
European customs tariff number	85444290
GTIN	5713140246218
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600