






LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AP	-		L	REV.BY ECO-11-020077	18OCT2011	HC	WLS
			L1	REV. BY ECO 13-016867	30OCT2013	HC	WLS
			L2	REVISED PER ECN-26-364588	20JAN2026	MK	AK

NOTES:

⚠ WIRE RANGE #22 TO #18 AWG; INSULATION RANGE 1,5 mm TO 2,8 mm [.060 TO .100 INCH]



POST-TIN OVER NICKEL	BRASS	LOOSE PIECE	61123-1
PRE-TIN	BRASS	STRIP PRODUCT	61064-3
PRE-TIN OVER NICKEL	BRASS	STRIP PRODUCT	61064-1
FINISH	MATERIAL	DESCRIPTION	PARTNUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H.C.CANTERI CHK W.L.STEFANI APVD -		11NOV2009 11NOV2009		 TE Connectivity							
DIMENSIONS: mm [inch]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME .060 COMBOLINE SOCKET									
		0 PLC ±- 1 PLC ±- 2 PLC ±0,31 (.012) 3 PLC ±- 4 PLC ±- ANGLES ±2°		PRODUCT SPEC 108-1002		-							
MATERIAL SEE TABLE		FINISH SEE TABLE		APPLICATION SPEC -		SIZE A3		CAGE CODE 00779		DRAWING NO C-61064		RESTRICTED TO -	
Customer Drawing				WEIGHT -		SCALE 10:1		SHEET 1		OF 1		REV L2	