



Part Number : 1301100034

Series Number : 130110

Product Category : Lamps and Lights

Product Description : Wet Location 70W Metal Halide Magnet Mount Area Light with Feed Thru, Cord Type 16/3 SJTOW, Cord Length 3.04m (10.0')

Status : Active

Engineering Number : 8565F-MH

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Lamps and Lights
Series	130110

Description	Wet Location 70W Metal Halide Magnet Mount Area Light with Feed Thru, Cord Type 16/3 SJTOW, Cord Length 3.04m (10.0')
NEMA Configuration	NEMA 5-15
NEMA Rating	NEMA 3
Product Family	Wide-Area Lighting Products
Product Name	Woodhead
Type	Wide Area Lamps
UPC	78678829572

Agency

UL	E174254
----	---------

Electrical

Lamp Wattage - Maximum	70W
Lumens	3600
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

Physical

Bulb Type	Metal Halide - Probe Start
Cord Length - Primary	3.04m (10.0')
Cord Length - Secondary	0.305m (1.0')
Cord Type - Primary	16/3 SJTOW
Cord Type - Secondary	16/3 SJTOW
Depth	207.26mm (8.160")
Duty	Wet Location
Guard Included	No
Guard Type	N/A
Height	264.16mm (10.400")
Lamp Type	MH70
Length	228.60mm (9.000")
Material - Globe	Clear Polycarbonate
Material - Guard	N/A
Mounting Style	Magnet

Net Weight	5597.325/g
Outlet	Feed-Through
Packaging Type	Carton

This document was generated on May 04, 2024