

Datasheet for part number MKJ1A7W9-19PA

Our Catalog Part Number: MKJ1A7W9-19PA
Our Global Manufacturing Part Number: 155143-1000
Brand: Cannon Product Category: Circular Product Line: Trinity MKJ Series: MKJ1

Product Datasheet	
Series	Threaded Coupling, Double Start ACME Thread
Class	Environmental Plug and Receptacle with Banding/Overmolding Attachment
Shell Style	Jam Nut Receptacle-Rear Panel Mount
Plating	Aluminum/OD Cad
Contact Arrangement	9-19
Contact Quantity	19
Contact Size	Size 23
Contact Gender	Pin, Crimp, Removable
Insulator Resistance	5000 Megaohms Minimum
Spacing	#23 / 0.076 inches (1.9 mm)
Wire Accommodation	#22 - #28 AWG
Current Rating	5 Amps Maximum
Voltage Rating	500 VAC RMS Sea Level
Operating Temperature	-55°/+150°
Contact Resistance	8 Milliohms Maximum
Vibration Resistance	20 g' in Accordance with MIL-STD-1344 Method 2005, Condition IV
Physical Shock	300 g in Accordance with MIL-STD-1344 Method 2004, Condition E
EMI Shielding Effectiveness	40dB Attenuation, 100 MHz to 1000 MHz

Specifications and dimensions subject to change.