© 2017 TE Connectivity Ltd. family of companies. All Rights Reserved

CONNECTORS

RACK & PANEL CONTACTS



✔ Active

TE CONNECTIVITY (TE)

SKT CONT ASSY,SZ 22,ARINC

AMP | CNT , SKT

208264-4
TE Internal Number: 208264-4

EU RoHS Compliant with Exemptions
EU ELV Compliant with Exemptions

Contact Type Socket

Contact Size 22

Contact Configuration Crimp Snap-In

Length 16.26 mm [.64 in]

Contact Mating Area Plating Material Gold

PRODUCT DRAWING
English

3D PDF

DOCUMENTATION

Product Drawings

ASSY, CONTACT, SOCKET, SIZE 22, ARINC 600

PDF **(TIFF AVAILABLE)**

English

CAD Files

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Downloaded from Arrow.com.

Customer View Model

2D_DXF.ZIP

English

3D PDF

PDF

English

Instruction Sheets

Instruction Sheet (U.S.)

Application Tooling For Screw-Machine Contacts

PDF

English

FEATURES

Please review product documents or contact us for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector & Contact Terminates To Wire & Cable
Product Type Contact

Body Features

Body Style Straight
Material Copper Alloy
Color Code Blue/Brown

Contact Features

Crimp Type Snap-In
Contact Angle Straight
Contact Type Socket
Contact Size 22
Contact Configuration Crimp Snap-In
Contact Mating Area Plating Material Gold
Contact Base Material Copper Alloy
Contact Mating Area Plating Thickness (µm) 1.27

Dimensions

Length 16.26 mm [.64 in]
Wire Range 26 – 22 AWG [.12 – .4 mm²]

Operation/Application

For Use With Mates with Pin

Packaging Features

Packaging Method Bag

Downloaded from Arrow.com.

PRODUCT COMPLIANCE

Statement of Compliance

Statement of Compliance

PDF

Downloaded from Arrow.com.