

Part Number : [936010688](#)

Product Description : Heavy-Duty Harsh Environment (HE) Single Lever Hood, Die-cast Aluminum, with 2 Pegs, Side Entry, Size 3A «21x21», M20 Thread, Black

Series Number : 93601

Status : Active

Product Category : Heavy-Duty Connectors

Engineering Part Number : 7803.6230.1



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	Heavy Duty Connectors
Series	93601
Description	Heavy-Duty Harsh Environment (HE) Single Lever Hood, Die-cast Aluminum, with 2 Pegs, Side Entry, Size 3A «21x21», M20 Thread, Black
Comments	IP67 with screw gasket.
Component Type	Single Lever Hood
IP Rating	IP66
Product Name	Heavy-Duty Connectors
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	HE
UPC	887191842752

Agency

CSA	256883
UL	E249674

Physical

Component Size	3A «21x21»
Entry Location	Side
Hood Coating	Polyester Powder
Hood Color	Black RAL 9005
Lock to Mating Part	Yes
Material - Hood	Die-cast Aluminum
Material - Peg	Die-cast Aluminum
Net Weight	20.900/g
Number of Pegs	2

Packaging Type	Bag
Thread Size	M20
Thread Type	(M) Metric

Mates With / Use With

Use with Part(s)

Description	Part Number
Use With	Size 3A «21x21» S-A, S-D, and S-Q Inserts

This document was generated on Jun 04, 2026