

WMRP MS

Item No: T0052919299N
Micro soldering iron WMRP MS 40 W, 12 V (handpiece without tips) for Active-Tip Heating Technology

KEY FEATURES

- Micro soldering iron 40 W, 12 V
- Military Standard
- For very small components with high energy demand
- For miniature works under a microscope
- For rework stations WR 3M and soldering station WT 2M.
- RT Soldering tips can be exchanged quickly and easily
- Active Tip (Cartridge)-System allows exchange of soldering tip despite a hot soldering iron
- Extremely short heating time
- Standby function

Downloaded from Arrow.com.

TECHNICAL DATA

Approximate Heating Time (50–350 °C/120–660 °F)	3 sec
ESD Safe	Yes
Integrated Direct Extraction	T0052918599
Power	40 W
Supply Unit	WD1M WR3M WD3M
Temperature Range (Depends on Tool)	93 - 454°C
Temperature Range °C	100 - 450 °C
Temperature Range °F	150 - 950 °F
Tip Range	RTM MS
Tip Type	RTM-MS
UPC	037103307873
Product Family	WT Soldering Irons

Downloaded from Arrow.com.