Data sheet

SDIS 0.5X3.0X100

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip

General ordering data

Version	Screwdriver, Screwdriver
Order No.	9008380000
Type	SDIS 0.5X3.0X100
GTIN (EAN)	4032248056347
Qty.	1 items
Delivery status	Discontinued
Available until	2021-06-30T00:00:00+02:00
Alternative product	SDIS 0.5X3.0X100

Downloaded from Arrow.com.

Data sheet

SDIS 0.5X3.0X100

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dimensions and weights

Width	205 mm	Width (inches)	8.0709 inch
Diameter	23 mm	Net weight	33 g

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	b28ab223-64ec-44cf-adb0-4dd6ebcae141

Technical data

Description of article	VDE-insulated screwdriver with slotted blade 0.5x3.0x100

Screwing tools

Blade width (B)	3 mm	Blade thickness (A)	0.5 mm
Form	Slotted	Blade length	100 mm
Blade type	B		

Classifications

ETIM 8.0	EC000158	ETIM 9.0	EC000158
ETIM 10.0	EC000158	ECLASS 14.0	21-04-04-07
ECLASS 15.0	21-04-04-07		

Downloaded from Arrow.com.