

LP-ADAPTER Han DD



Image is for illustration purposes only. Please refer to product description.

Part number	09 16 000 9905
Specification	LP-ADAPTER Han DD
HARTING eCatalogue	https://harting.com/09160009905

Identification

Category	Accessories
Type of accessory	PCB adapter
Description of the accessory	In the Han DD [®] crimp insert
	In the Han DD [®] module
	In the Han [®] DDD module (different electrical data: 7.5 A 160 V 2.5 kV 3)

Version

Gender	Male
	Female
Details	for PCB's up to 1.6 mm

Technical characteristics

Rated current	7.5 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	3
Limiting temperature	-40 ... +125 °C

Material properties

Material (insert)	Polyamide (PA)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R26

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
----------	--

Commercial data

Packaging size	10
Net weight	2 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140572812
eCl@ss	27460201 PCB connector (board connector)
UNSPSC 24.0	39121415