QUARTZ CRYSTAL MHZ


Part Number: 830105625401 | CFPX-180

AKA Number: LFXTAL056254

General Information

Standard 3.2 x 2.5mm SMD crystal in a ceramic package with a seam sealed metal lid, hermetically sealed.


Dimensions [mm]



Pad No	Pad Connection
1	Crystal
2	GND & Lid
3	Crystal
4	GND & Lid



Recommended Land Pattern [mm]



Downloaded from Arrow.com.

QUARTZ CRYSTAL MHZ

Part Number: 830105625401 | CFPX-180

AKA Number: LFXTAL056254

Frequency Parameters

Frequency	12.50 MHz
Frequency Tolerance	± 30 ppm @25°C
Frequency Stability	± 50 ppm
Operating Temperature	-40 °C to 85 °C
Overtone Order	Fundamental
Ageing	± 5 ppm max per year @ 25 °C

Material Parameters

Termination Finish	Ni Au
Moisture Sensitivity Level (MSL)	Not Applicable

Manufacturing Details

Reflow: 260 °C max over 10 seconds.

Electrical Parameters

Load Capacitance C_L	20 pF
Shunt Capacitance C_0	7 pF max.
Drive Level	100 µW max.
ESR	120 Ω max.

Environmental Parameters

Storage Temperature Range:	-55 °C to 125 °C

- Shock: 1500 g, 0.5 ms, 3 times in each of the 3 mutually perpendicular planes.
- Vibration: MIL-STD-883F, 20 g (20 Hz ~ 2000 Hz), 1.52 mm amplitude, 20 minutes in 3 mutually perpendicular planes, 4 cycles.

Technical Standards

RoHS Status	2015/863/EU - Compliant
REACH Status	(EC)1907/2006 - Compliant

Packaging Details

Packaging SPQ	Tape & Reel 3000 pcs

Tape & reel in accordance with EIA-481
Quantities below the standard reel size to be supplied on cut tape.

Company Address

IQD Frequency Products Ltd.
Station Road
Crewkerne
Somerset
TA18 8AR, United Kingdom

Downloaded from Arrow.com.