



[Aluminium enclosures](#)
[Plastic enclosures](#)

With flanges

[DIN rail](#)
[Hand-held](#)
[Sealed](#)
[Desktop](#)
[Electronic](#)
[19 inch rack](#)

[Accessories for enclosures](#)



The selection of enclosures

Selection of necessary enclosures for electronics on the size and main characteristics

AEK GmbH –
Electrical Enclosures, 60322, Deutschland, Frankfurt am Main, Falkensteiner str 77



G258CMF

[Enclosures](#) / [Plastic](#) / [Plastic box with flanges](#) / [G2xxCMF](#) / [G258CMF](#)

Sealed enclosure with clear lid and the flanges

G258CMF – Sealed enclosure with clear lid and the flanges light gray color with flanges for wall mounting or mounting on a place of installation, production is made of polycarbonate. Provides protection against dust and moisture according to the standard IP65. The package includes a transparent cover. Overall dimensions are: length 160mm, width 80mm, height 55mm. On the inner surface of the case cast stand for horizontal PCB mounting.

Price per box — € 8.34

1+

Price per box — on request

100+

PN: G258CMF

Packing: 80

Datasheet

Technical documentation in PDF format



[G258CMF, PDF-file - 59.741K6](#)

Quickly view [G258CMF PDF online](#) with Google Docs Viewer.



[Gasket parameters download, PDF-file - .K6](#)

Characteristics

Dimensions, mm	160x80x55
Material	Polycarbonate
Color	Light gray
Cover	Clear
PCB mounting	Horizontally, the racks
Waterproof	Yes
Ingress Protection Rating	IP65

series G2xxCMF

Sealed enclosure with the flanges and transparent cover

- [G200CMF](#)
- [G201CMF](#)
- [G203CMF](#)
- [G205CMF](#)
- [G212CMF](#)
- [G218CMF](#)
- [G221CMF](#)
- [G223CMF](#)
- [G232CMF](#)
- [G250CMF](#)
- [G256CMF](#)
- G258CMF**
- [G265CMF](#)
- [G278CMF](#)
- [G279CMF](#)
- [G2691CMF-IP67](#)
- [G2385CMF-IP67](#)
- [G200CMF-IP67](#)
- [G201CMF-IP67](#)
- [G203CMF-IP67](#)
- [G205CMF-IP67](#)
- [G212CMF-IP67](#)
- [G214CMF-IP67](#)
- [G218CMF-IP67](#)
- [G221CMF-IP67](#)
- [G223CMF-IP67](#)
- [G232CMF-IP67](#)
- [G250CMF-IP67](#)
- [G256CMF-IP67](#)
- [G258CMF-IP67](#)
- [G265CMF-IP67](#)
- [G278CMF-IP67](#)
- [G279CMF-IP67](#)
- [P200CMF-IP68](#)
- [P201CMF-IP68](#)
- [P203CMF-IP68](#)
- [P205CMF-IP68](#)
- [P212CMF-IP68](#)
- [P214CMF-IP68](#)
- [P218CMF-IP68](#)
- [P221CMF-IP68](#)
- [P223CMF-IP68](#)
- [P232CMF-IP68](#)
- [P250CMF-IP68](#)
- [P256CMF-IP68](#)
- [P258CMF-IP68](#)
- [P265CMF-IP68](#)
- [P278CMF-IP68](#)
- [P279CMF-IP68](#)
- [P2385CMF-IP68](#)
- [P2691CMF-IP68](#)
- [G214CMF](#)
- [G2393CMF](#)
- [G2393CMF-IP67](#)
- [P2393CMF-IP68](#)

Sealed enclosure with the flanges and transparent cover is made of polycarbonate. The base is equipped with mounting flange for durable attachment. Provides protection against dust and moisture according to the IP65 (IEC 529) and NEMA 4 standard.

Electrical Enclosures



HQ009

[Aluminium enclosure](#), production is made of aluminum alloy ADC-12, finishing surface of natural aluminum color.



G2102

[Sealed enclosure](#), production is made of polycarbonate, finishing surface of light gray color, ingress protection rating IP65.



G1600260

[Handle for G758, G753, G754, G731, G733 enclosures](#), production is made of nylon66 UL94-V2, finishing surface of light gray color.