



Part Number : [1300580025](#)

Product Description : Ultra-Lock (M12) D-Coded to RJ-45 Adapter, Straight to Straight, 4-Pole Female to RJ45 Male, Unshielded PVC, 1.0m (3.28') Length

Series Number : 120109

Status : Obsolete

Product Category : Circular Industrial Connectors

Engineering Part Number : ERWPAB3002M010



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Obsolete
Category	Circular Industrial Connectors
Series	120109
Description	Ultra-Lock (M12) D-Coded to RJ-45 Adapter, Straight to Straight, 4-Pole Female to RJ45 Male, Unshielded PVC, 1.0m (3.28') Length
IP Rating	IP67
Product Name	RJ45,Ultra-Lock (M12)
Type	Double Ended
UPC	78678802441

Agency

UL	E200650
----	---------

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	250V AC/DC

Physical

Coupling Type	Push to Lock
Gender	Female-Male
Keyway	D-Coded
Length	1.0m
Material - Component	Nickel-plated Brass
Mounting Thread Size	PG9
Orientation	Straight
Panel Mount	Back
Poles	4
Temperature Range - Operating	-25° to +80°C

Wire/Cable Type	Unshielded PVC
Wire Size (AWG)	24

This document was generated on May 21, 2026

Obsolete