

Part Number: **5690714400F**

General Description	
Series	569
Configuration	3 mm Lens
Description	3 mm Bi -Level CBI Y/G - Y/G
Package Options	Bulk Packaging
Sizes	3mm
Lamp Type	Bi -Level Housing
Viewing	Right Angle
Polarity	Cathode Pin 1 & 3
Lens Style	Untinted, Diffused
Viewing Angle	80
LED Centerline	2.29mm

Absolute Maximum Ratings (Ta = 25Â°)	
Solder Temperature	260 for 5 secs
Operating Temperature	-55 to +100
Storage Temperature	-55 to +100

Operating Characteristics		
	LED Position: 1,2	
Color	Yellow	Green
Peak Wave Length	585	565
Luminous Intensity Min	2.5	2.5
Luminous Intensity Typical	4.3	6.3
Forward Voltage Typical	2.1	2.1
Forward Voltage Max	2.8	2.8
Power Dissipation Max	60mW	100mW



5690714400F

check stock



[This is a RoHS Compliant Product](#)
[To learn more click here](#)