



5.0

1 Review



5.0

1 Review

 Need Help?[← Browse All Products](#) | [Cat5e / Cat6 / Cat6a](#) | [Cat6](#) | [Cat6 Plenum Patch Cables](#)

Loading...

# 10ft Cat6 Non-Booted UTP Unshielded Ethernet Network Patch Cable - Plenum CMP-Rated - Gray (TAA Compliant)

For network adapters, hubs, switches, routers, DSL/cable modems, patch panels and other high performance networking applications where plenum cables are required.

 Roll over image to zoom in


5.0


1 Review

Product # : 15268

Connector 1 : (1) RJ-45 Male

Connector 2 : (1) RJ-45 Male

Colors :



Lengths :

[+ show all lengths](#)In Stock, only 2 left  Add**Need It shipped today?**

Place your order before the timer runs out!



02: 44: 50

 print  share  chat Product Info Customer Reviews Questions & Answers Distributors

... More Choices

 Description Features Certifications Specs Uses**Product Description**

Strict building code requirements for cabling in plenum spaces have created installation challenges in settings such as schools, hospitals and other commercial buildings. C2G has expanded its connectivity portfolio to include a line of cables that are ideal for routing through plenum space above dropped ceilings or under raised floors.

Applications include voice/data/video distribution; this cable will handle bandwidth-intensive applications. Meets all Cat6 TIA/EIA standards, and reduces both impedance and structural return loss (SRL).

Constructed from high quality plenum cable, this design minimizes Near-End Crosstalk (NEXT) levels. Available in Gray, Blue and Black to easily color-code your network installation.

**Product Features**

- Rated for Plenum, in-wall installations
- Cat6 cable with standard RJ45 connectors
- Available in lengths up to 100ft

**WARNING:** Cancer and Reproductive Harm [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)



## Product Specifications

<b>Color :</b>	Grey
<b>Length :</b>	10.00 Foot
<b>Jacket Rating :</b>	Plenum
<b>UPC :</b>	757120152682
<b>Warranty :</b>	Lifetime
<b>Vendor :</b>	C2G
<b>Weight :</b>	0.253 LB

- Conductor: 4-pair (UTP) 23AWG solid copper
- Jacket Rating: CMP - Plenum
- Connectors: 50 micron gold plated RJ45
- Wired: 568B
- Tested to 550MHz
- TIA/EIA-568-C.2
- RoHS Compliant

## Product Uses

- 100Base T Ethernet
- 1000Base-T Gigabit Ethernet
- 10GBase-T 10 Gigabit
- Ethernet
- 1000 Mbps ATM
- 622Mbps ATM
- Broadband Video
- POE

## Info

[About Us](#)  
[Order History](#)  
[Where To Buy](#)  
[More ▾](#)

## Service

[Contact Us](#)  
[OEM Solutions](#)  
[Tech Support](#)  
[More ▾](#)

## Resources

[Connector Guides](#)  
[ConnectXpress](#)  
[Drivers & Manuals](#)  
[More ▾](#)

## Have A Question?

Get help with [Chat](#)  
Call C2G **800.506.9607**



United States | Europe +

Copyright © 2019 C2G. All Rights Reserved



