





REVISIONS	
A	CO-95348-B
DLM	
16 FEB 00	
B	0010299
TCC-AP	
27 DEC 04	

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	
OPERATING FORCE	6-13 LB
FULL OVERTRAVEL FORCE	30 LB MAX
RELEASE FORCE	4 LB MIN
PRETRAVEL	.100 MAX
DIFFERENTIAL TRAVEL	.020 MIN
OVERTRAVEL	.180 MIN

ELECTRICAL DATA		
CONTACT ARRANGEMENT		
1X S P N C 1X S P N O		
LOAD	28 VDC	
	SEA LEVEL	50,000 FT.
RES	4	4
IND	2	2
MOTOR	4	

THIRD ANGLE PROJECTION		
		
SCALE FULL		
DO NOT SCALE PRINT		
UNLESS OTHERWISE SPECIFIED TOLERANCES ARE		
ONE PLACE	(.0)	±.030
TWO PLACE	(.00)	±.015
THREE PLACE	(.000)	±.005
ANGLES		±
WEIGHT 6.0 OZ MAX		

NOTES

- 1 - SWITCH SEALED PER MIL-PRF-8805 SYMBOL 2
- 2 - COINCIDENCE OF OPERATING AND RELEASING POINTS: .010. OF PLUNGER TRAVEL
- ③ - CATALOG LISTING, MICRO IDENTIFICATION, CIRCUIT DIAGRAM AND DATE CODE ARE SHOWN ON NAMEPLATE
- ④ - HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-PRF-8805