






length in "1m" step	40	XXX=400
	39	XXX=390
	.	.
	12	XXX=120
length in "0.1m" step	11	XXX=110
	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	.	.
	0.4	XXX=004
	0.3	XXX=003
	0.2	XXX=002
	0.1	XXX=001
Step	a [m]	XXX

4.0 to 40	+1%
0.1 to 3.9	+0.04
a [m]	Tolerance

Part no.	213480813XXXXX
----------	----------------

Type of cable	XX
PVC grey, 3x0.25mm ²	XX=80
PUR black, 3x0.25mm ²	XX=88

- Protection level: IP67
- Temperature range: -25°C ... +80°C



All Dimensions in mm
Original Size DIN A3

Scale
2:1

Free size tol.

Ref.
Sub.

All rights reserved
Department EC PD - RO

HARTING Electronics GmbH
D-32339 Espelkamp

Created by
POPESCU

Inspected by
AVRAM

Standardisation
HOFFMANN

Date
2015-12-17

State
Final Release

Title
M8 Cable Assembly

Type
TB

Number
213480813XXXXX

Doc-Key / ECM-Nr.
100577987/UGD/009/B
500000098541

Rev.
B

Page
1/1