


[Connectors](#) > [Pluggable IO Connectors & Cages](#) > [CFP/CFP2/CFP4](#)

Heatsink Assembly, CFP



CFP

TE Part # **2274283-1**

TE Internal #: **2274283-1**

Form Factor : **CFP**

Product Type : **Accessory**

Included Heat Sink : **Yes**

Heat Sink Style : **Fin**

Heat Sink Height : **5 mm [.197 in]**

[Similar Products](#)

Compatible Parts & Tooling

Price (USD):

\$103.50

[Volume pricing](#) +

✓ **25 IN TE STOCK**

QTY:

1

Subtotal: **\$103.505**



ADD TO CART

SHOP OUR DISTRIBUTORS

North America

[See all price breaks](#)

Distributor	1	10,000	Buy
DIGI-KEY ELECTRONICS	\$93.840	\$76.248	Visit Site
25 in stock			

We are here to help!

Get in touch with our product experts.



CHAT WITH US



EMAIL US



CALL US

DOCUMENTS

FEATURES

PRODUCT COMPLIANCE

Product Drawings

Heatsink Assembly, CFP

[Heatsink Assembly, CFP](#) English

CAD Files

3D PDF

[3D_CVM_CVM_2274283-1_B.pdf](#) 3D

Customer View Model

[ENG_CVM_CVM_2274283-1_B.2d_dxf.zip](#)

English

[ENG_CVM_CVM_2274283-1_B.3d_igs.zip](#)

English

[ENG_CVM_CVM_2274283-1_B.3d_stp.zip](#)

English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features

Product Line : **CFP**

Form Factor : **CFP**

Product Type : **Accessory**

Included Heat Sink : **Yes**

	Pluggable I/O Accessory Type : Heat Sink
Electrical Characteristics	Data Rate (Max) (Gb/s): 100
Body Features	Heat Sink Style : Fin Heat Sink Height : 5 mm [.197 in] Heat Sink Finish : Anodized Black
Dimensions	PCB Thickness (Recommended) : 2 mm [.079 in]
Operation/Application	For Use With Pluggable I/O Products : CFP Assembly
Packaging Features	Packaging Method : Box & Tray
Statement of Compliance	Statement of Compliance pdf

Also in the Series | [CFP](#)



CFP/CFP2/CFP4 (22)

