

CT3978

Datasheet

Probe Body Fixed Tip Kit w/Full Accessories

Pair compact probe bodies w/2 mm (.080") probe tips with...

Description

Pair of DMM probe bodies with 2 mm (.080) diameter x 19 mm (0.75) probe tips for all test applications. With safety cap installed, the probe meets 600 V CAT IV applications. Remove the safety cap for access to the standard 2mm tip and to attach tip accessories.

Includes pair of extended tips, alligator clips, spade lugs and sprung hooks all featuring "snap-locks" to probes.

Features:

- Probe body with 4mm sheath banana jack connection
- IEC 61010-031 rated
- Accessories "snap-lock" to probe bodies
- Cap on probe tip provides CAT III/CAT IV usage

Kit Contains:

- (2) Probe Bodies, black & red - (CT3975)
- (2) Extended Tips, black & red - (CT3941)
- (2) Alligator Clips, black & red - (CT3943)
- (2) Spade Lugs, black & red - (CT3945)
- (2) Spring Hooks, black & red - (CT3947)



Technical data subject to change.

© Cal Test Electronics 2018.

caltestelectronics.com



All specifications apply to the unit after a temperature stabilization time of 20 minutes over an ambient temperature range of 25°C ± 5°C.

Specifications

Values	Probe Bodies	Extended Tips	Alligator Clips	Spade Lugs
Voltage	1,000 V CAT III / 600 V CAT IV w/cap1,000 V CAT II w/o	300 V CAT IV w/cap1,000 V CAT II w/o	300 V CAT II w/o	<30 Vac / <60 V
Current	10 A	3 A	5 A	5 A
Temperature (degrees)	-20 to +80C			
RoHS (2011/65/EU)	Compliant			

Specifications are subject to change without notice. To ensure the most current version of this manual, please download the current version from our website: caltestelectronics.com

Technical data subject to change.

© Cal Test Electronics 2018.

caltestelectronics.com

