





	1	2	3	4	5	6	7																																																																																		
A								A																																																																																	
B								B																																																																																	
C	Conductor: [26AWG(0.16/7)Bare Copper]x4C Insulation: [PP6331 ID:0.95±0.03]x4C Jacket: PVC NOUL 65P 							C																																																																																	
D	 A, B, C, D							D																																																																																	
E	 E, F, G							E																																																																																	
F	Note for plug: - Material: Housing-polycarbonate, clear. - Terminal-0.36[.014] thick phosphor bronze. - Thick gold in localized gold plate. - Area, Gold Flash over the remainder. - Over 2.54mm[.000100] thick nickel underplate.							F																																																																																	
	<table><tr><th>Part Number</th><th>Drawing Number</th><th>Wire Length "L"</th><th>Jacket Color</th><th>Cut Length</th></tr><tr><td>AT-S-26-6/4/B-5/R</td><td>A</td><td>1,525±20(5ft)</td><td>Black</td><td>1,525-1,535mm</td></tr><tr><td>AT-S-26-6/4/B-7/R</td><td>B</td><td>2,135±30(7ft)</td><td>Black</td><td>2,135-2,145mm</td></tr><tr><td>AT-S-26-6/4/B-10/R</td><td>C</td><td>3,050±60(10ft)</td><td>Black</td><td>3,050-3,060mm</td></tr><tr><td>AT-S-26-6/4/B-12/R</td><td>D</td><td>3,660±60(12ft)</td><td>Black</td><td>3,660-3,670mm</td></tr><tr><td>AT-S-26-6/4/B-14/R</td><td>E</td><td>4,270±60(14ft)</td><td>Black</td><td>4,270-4,280mm</td></tr><tr><td>AT-S-26-6/4/B-25/R</td><td>F</td><td>7,625±100(25ft)</td><td>Black</td><td>7,625-7,635mm</td></tr><tr><td>AT-S-26-6/4/B-50/R</td><td>G</td><td>15,250±150(50ft)</td><td>Black</td><td>15,250-15,260mm</td></tr></table>							Part Number	Drawing Number	Wire Length "L"	Jacket Color	Cut Length	AT-S-26-6/4/B-5/R	A	1,525±20(5ft)	Black	1,525-1,535mm	AT-S-26-6/4/B-7/R	B	2,135±30(7ft)	Black	2,135-2,145mm	AT-S-26-6/4/B-10/R	C	3,050±60(10ft)	Black	3,050-3,060mm	AT-S-26-6/4/B-12/R	D	3,660±60(12ft)	Black	3,660-3,670mm	AT-S-26-6/4/B-14/R	E	4,270±60(14ft)	Black	4,270-4,280mm	AT-S-26-6/4/B-25/R	F	7,625±100(25ft)	Black	7,625-7,635mm	AT-S-26-6/4/B-50/R	G	15,250±150(50ft)	Black	15,250-15,260mm																																										
Part Number	Drawing Number	Wire Length "L"	Jacket Color	Cut Length																																																																																					
AT-S-26-6/4/B-5/R	A	1,525±20(5ft)	Black	1,525-1,535mm																																																																																					
AT-S-26-6/4/B-7/R	B	2,135±30(7ft)	Black	2,135-2,145mm																																																																																					
AT-S-26-6/4/B-10/R	C	3,050±60(10ft)	Black	3,050-3,060mm																																																																																					
AT-S-26-6/4/B-12/R	D	3,660±60(12ft)	Black	3,660-3,670mm																																																																																					
AT-S-26-6/4/B-14/R	E	4,270±60(14ft)	Black	4,270-4,280mm																																																																																					
AT-S-26-6/4/B-25/R	F	7,625±100(25ft)	Black	7,625-7,635mm																																																																																					
AT-S-26-6/4/B-50/R	G	15,250±150(50ft)	Black	15,250-15,260mm																																																																																					
G	Unit: mm RoHS Compliant <table><tr><th>Scale</th><th>Free</th><th></th><th></th><th></th><th></th><th>Date</th><th>Name</th><th>Title</th></tr><tr><td>TOLERANCE</td><td></td><td></td><td></td><td></td><td></td><td>Drawn</td><td>28.06.13</td><td>Wilson</td></tr><tr><td>X.</td><td>±X</td><td></td><td></td><td></td><td></td><td>Approved</td><td>28.06.13</td><td>Groll</td></tr><tr><td>X.X</td><td>±X</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>X.XX</td><td>±X</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>DIM</td><td>TOL</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>X.°</td><td>±X°</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>X.X°</td><td>±X°</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>Angle</td><td>TOL</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr></table>							Scale	Free					Date	Name	Title	TOLERANCE						Drawn	28.06.13	Wilson	X.	±X					Approved	28.06.13	Groll	X.X	±X								X.XX	±X								DIM	TOL								X.°	±X°								X.X°	±X°								Angle	TOL								G
Scale	Free					Date	Name	Title																																																																																	
TOLERANCE						Drawn	28.06.13	Wilson																																																																																	
X.	±X					Approved	28.06.13	Groll																																																																																	
X.X	±X																																																																																								
X.XX	±X																																																																																								
DIM	TOL																																																																																								
X.°	±X°																																																																																								
X.X°	±X°																																																																																								
Angle	TOL																																																																																								
H	1940 W. Drake Drive, Suite 101 • Tempe, AZ 85283 Toll Free: 1-877-277-6266 • Email: info@assmann.us ASSMANN WSW components <table><tr><th>Id.</th><th>Modification</th><th>Date</th><th>Name</th><th>Replace</th><th>Sheet</th></tr><tr><td></td><td></td><td></td><td></td><td></td><td>1/1</td></tr></table>							Id.	Modification	Date	Name	Replace	Sheet						1/1	H																																																																					
Id.	Modification	Date	Name	Replace	Sheet																																																																																				
					1/1																																																																																				
	1	2	3	4	5	6	7																																																																																		

Downloaded from [Arrow.com](#)