

RETURN TO: [DIGI XBEE INDUSTRIAL GATEWAY](#)

AC Power Supply - Std Temperature, Universal plugs (US, EU, UK, AU) to 5VDC - 2.5mm locking barrel plug

PART NUMBER: 76002021

[VIEW PURCHASE OPTIONS ▼](#)




[Contact us](#)

Compatibility:	TransPort WR11XT
Rated input voltage rating:	100VAC to 240VAC
Input frequency:	47 Hz to 63 Hz
Max. in-rush current:	30A typical at 115VAC
Input Plug Type:	Includes four input connectors: NA, EU, UK, and AU
Leakage current:	<3.5mA at 240VAC
Output Voltage:	5VDC
Load current:	0.6a RMS max
Output Plug:	5.5 x 2.5 x 11mm barrel plug
Max. output power:	15W
Operating Temperature:	0°C to 40° C
Storage Temperature:	-10°C to -80° C
Size:	74 x 43.5 x 34 mm
Cord Length:	6ft
Certifications:	UL, cUL , CE


RECENTLY VIEWED



AC Power Supply -
Std Temperature,
Universal plugs (US,
EU, ...



DB9F/Bare Wire 48"
Cable




XTend-PKG 900 MHz,
commercial, USB,
w/ accessories, 128-
bit ...



EEPROM, serial,
w/MAC address,
Surface-Mount

Contact a Digi expert and get started today! [CONTACT US ►](#)



About Digi

News

Events

Locations

Leadership

Support

Careers

Investor Relations

Partners

How to Buy

Export Compliance

Quality &
Environment

Newsletter Sign Up

Other Digi Sites

Legal

Privacy Policy

Cookie Policy

Site Map

Internet of Things development
with #wireless communications
presents many questions and
requires important consider...
<https://t.co/UQuOH1W9gD>

Fri Sep 28 2018



This website uses cookies that are essential to the operation of this site, to personalize content and allow us to analyze site performance. If you continue to use our website, you consent to the use of our cookies. Click OK to indicate your acceptance of our [cookie policy](#), including advertising cookies, analytics cookies, and sharing of information with social media, advertising and analytics partners.

Copyright 1996-2018 Digi International Inc. All rights reserved.

OK ►

HAVE A QUESTION?

X

