
Your Expert Partner for **Human Machine Interfaces**

Actuator


61-
4970.13



https://www.eao.com/component/61-4970.13/en/a...

Downloaded from Arrow.com.

Your product:



61-4970.13
Actuator

FRONT

Front dimension:	24 mm x 24 mm
Front form:	Square
Front bezel colour:	Black
Front bezel material:	Plastic

MOUNTING

Mounting cut-out:	21.2 mm x 21.2 mm
Mounting type:	Panel mounting

ELECTRICAL CHARACTERISTICS

Power (W):	1
Resistance:	10 kΩ

MECHANICAL CHARACTERISTICS

Terminal:	Flat ribbon cable
Tightening torque:	Max. 0.5 Nm
Weight:	0.015 kg

AMBIENT CONDITION

IP front protection:	IP65
Operating temperature:	– 25 °C … + 55 °C

Downloaded from Arrow.com.

CERTIFICATE

REACH: REACH compliant

RoHS: RoHS compliant


OTHER

Short Description: Actuator, 21.2 mm x 21.2 mm, 24 mm x 24 mm, Square, Black, Plastic, Flat ribbon cable, IP65

Housing material: Plastic


Product attributes: Cable length 300 mm

Wiring diagrams:



A = blue
B = red
C = yellow


Component layouts:




A = Terminals (rear side)
B = Conductor colour of flat ribbon cable
C = a = blue, b = red, c = yellow

Mounting cut-outs:

Downloaded from Arrow.com.



Dimension drawings:



Downloaded from Arrow.com.