

# Aptiv Connection Systems Catalog

Customer Service

Samples Request

Find by Feature

Browse by Category

Browse by Application

Comparison List (0)

Share

Enter part number or keyword

Search

Search Results (1)

Search Options

1 Result(s): [ All ] - 10738192

☐ Compare

211CC2S1230 - Scima2 1.5 Female  
☐ Unsealed Gold Plating Terminal,  
Cable Range 0.35 - 0.75 mm2

☐ Compare

## Scima2 1.5 Female Unsealed Gold Plating Terminal, Cable Range 0.35 - 0.75 mm2

Part # 211CC2S1230



[Question about this product?](#)

Attributes

Documents (1)

|                                          |                                                                                                                                                                                                     |
|------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Part # :                                 | 211CC2S1230                                                                                                                                                                                         |
| Description :                            | Scima2 1.5 Female Unsealed Gold Plating Terminal, Cable Range 0.35 - 0.75 mm2                                                                                                                       |
| Product Type :                           | Terminal                                                                                                                                                                                            |
| Status :                                 | ✓ Active                                                                                                                                                                                            |
| Blade size [mm] :                        | 1.5                                                                                                                                                                                                 |
| Series :                                 | 1.5                                                                                                                                                                                                 |
| Gender :                                 | Female                                                                                                                                                                                              |
| Sealable :                               | Sealed                                                                                                                                                                                              |
| Material :                               | CuMg                                                                                                                                                                                                |
| Weight [g] :                             | 1                                                                                                                                                                                                   |
| Plating :                                | Gold                                                                                                                                                                                                |
| Maximum Cable Diameter [mm] :            | 2.60                                                                                                                                                                                                |
| Minimum Cable Core Cross Section [mm2] : | 0.35                                                                                                                                                                                                |
| Maximum Cable Core Cross Section [mm2] : | 0.75                                                                                                                                                                                                |
| Remarks :                                | Former FCI Product, Delphi PN:10738192, SICMA 2, One piece construction, High current carrying capacity, Low contact mating force, Class 4, temperature C, Suitable for secondary lock, Gold Plated |

Certain products listed on this website may be subject to restricted usage or distribution or may not be available. For additional information, please contact your local sales office.