

[\(/en\)](#)

Search



AMD EPYC™ 7601 ▼

[SPECIFICATIONS](#)[DRIVERS & SUPPORT \(/EN/SUPPORT/CPU/AMD-EPYC/AMD-EPYC-7001-SERIES/AMD-EPYC-7601\)](/EN/SUPPORT/CPU/AMD-EPYC/AMD-EPYC-7001-SERIES/AMD-EPYC-7601)

AMD EPYC™ 7601

[Share this page](#)

AMD EPYC™ 7601

Specifications

of CPU Cores: 32**# of Threads:** 64**Base Clock:** 2.2GHz**Max Boost Clock:** Up to 3.2GHz**All Core Boost Speed:** 2.7GHz**Total L3 Cache:** 64MB**Package:** SP3**Socket Count:** 1P/2P

PCI Express® Version: PCIe 3.0 x128

Default TDP / TDP: 180W

System Memory

System Memory Specification: 2666MHz

System Memory Type: DDR4

Memory Channels: 8

Per Socket Mem BW: 170.6 GB/s

Key Features

Workload Affinity

Capacity HPC

DBMS and Analytics

Foundation

Product Family: AMD EPYC™

Product Line: AMD EPYC™ 7001 Series

Platform: Server

OPN Tray: PS7601BDVIHAF

OPN PIB: PS7601BDAFWOF

Related Products

AMD EPYC™ 7551P (/en/products/cpu/amd-epyc-7551p)

of CPU Cores: 32

of Threads: 64

Max Boost Clock: Up to 3.0GHz

Base Clock: 2.0GHz

Default TDP / TDP: 180W

[LEARN MORE \(/EN/PRODUCTS/CPU/AMD-EPYC-7551P\)](/EN/PRODUCTS/CPU/AMD-EPYC-7551P)

AMD EPYC™ 7551 (/en/products/cpu/amd-epyc-7551)

of CPU Cores: 32

of Threads: 64

Max Boost Clock: Up to 3.0GHz

Base Clock: 2.0GHz

Default TDP / TDP: 180W

[LEARN MORE \(/EN/PRODUCTS/CPU/AMD-EPYC-7551\)](/EN/PRODUCTS/CPU/AMD-EPYC-7551)

AMD EPYC™ 7501 (/en/products/cpu/amd-epyc-7501)

of CPU Cores: 32

of Threads: 64

Max Boost Clock: Up to 3.0GHz

Base Clock: 2.0GHz

Default TDP / TDP: 155/170W

[LEARN MORE \(/EN/PRODUCTS/CPU/AMD-EPYC-7501\)](/en/products/cpu/amd-epyc-7501)

[LOAD MORE \(?PAGE=1\)](#)

[Our Company \(/en/corporate/about-amd\)](/en/corporate/about-amd) [Newsroom \(/en/corporate/newsroom\)](/en/corporate/newsroom)
[Careers \(/en/corporate/careers\)](/en/corporate/careers) [Investors \(http://ir.amd.com\)](http://ir.amd.com) [Contact Us \(/en/corporate/contact\)](/en/corporate/contact)



©2020 Advanced Micro Devices, Inc

[Terms and Conditions \(/en/corporate/copyright\)](/en/corporate/copyright) [Privacy \(/en/corporate/privacy\)](/en/corporate/privacy) [Cookie Policy \(/en/corporate/cookies\)](/en/corporate/cookies)

[Trademarks \(/en/corporate/trademarks\)](/en/corporate/trademarks)

[Statement on Forced Labor \(https://www.amd.com/system/files/documents/statement-human-trafficking-forced-labor.pdf\)](https://www.amd.com/system/files/documents/statement-human-trafficking-forced-labor.pdf)

[Fair and Open Competition \(/en/corporate/competition\)](/en/corporate/competition) [UK Tax Strategy \(https://www.amd.com/system/files/documents/amd-uk-tax-strategy.pdf\)](https://www.amd.com/system/files/documents/amd-uk-tax-strategy.pdf)