


THESE DRAWINGS ARE THE PROPERTY OF QUALTEK ELECTRONICS AND NOT TO BE REPRODUCED FOR OR COMMUNICATED TO A THIRD PARTY WITHOUT THE EXPRESS WRITTEN PERMISSION OF AN OFFICER OF QUALTEK ELECTRONICS.

REVISION			
REV.	DESCRIPTION	DATE	APPROVED
B	Updated Specifications	08-12-13	LY



- NOTES:
- CABLE: UL20276
(30AWG*1PR+EAM)*2C+30AWG*1PR+24AWG*2C+AEB (AL) 65%
OUTER JACKET: BLACK, OD: 5.5 ± 0.2mm
 - CONNECTOR: MICRO USB 3.0 A TYPE MALE
INSULATOR: BLACK
PIN G/F
NICKEL PLATED SHELL
 - CONNECTOR: MICRO USB 3.0 B TYPE MALE
INSULATOR: BLACK
PIN G/F
NICKEL PLATED SHELL
 - PVC MOLDED: 45P BLACK
 - ELECTRICAL TEST:
<1>.100% OPEN SHORT & MISS WIRE TEST
<2>.INSULATION RESISTANCE: DC300V 20M ohm MIN.
<3>.CONDUCTOR RESISTANCE: 2 ohm MAX.

CONTROLLED

Dim range (mm)	Tolerance +/- (mm)	Qualtek Electronics Corp. WCI DIVISION		
		Part Number: 3023007-01M RoHS Compliant		
0-1	0.15	Description: MICRO USB 3.0 A/M - MICRO USB 3.0 B/M		
1-6	0.20			
6-18	0.30	UNIT: mm	REV.B	
18-50	0.50		Approved / Date	
50-120	0.70	Drawn / Date	Checked / Date	Approved / Date
120-250	0.90	R.Nuti 06-25-10	06-25-10	LY / 06-25-10
250-500	1.20			