

COTS Micro-D Pigtails - Insulated Wire Plastic Shell



Factory-terminated Micro-D connectors are available with three standard wire types for commercial, military and aerospace needs. All plastic bodies offer an economical alternative to Micro-D metal shell versions.

- #24 thru #30 AWG
- Economical, non-environmental
- 9 thru 51 contacts
- Precision crimp terminations

Note: Micro-D plastic connectors are not intermatable with metal shell connectors.



RELATED INFORMATION

Performance Specifications	IBC*
Materials and Finishes	IBC*
Contact Arrangements	7-8
Panel Cutouts, Mounting Dimensions	9
Standard Dimensions	10
Jacking Hardware Kits	C-3,4

* Available on the Inside Back Cover Fold-Out

HOW TO ORDER

Conn. Series	Housing Material Table I*	No. of Contacts	Contact Type	Wire Gage (AWG)	Wire Type Table IV*	Wire Color Table IV*	Wire Length	Hardware Table V*
MWD	L – LCP (Liquid Crystal Polymer)	9	P – Pin S – Socket	4 - 24	E - Std K - Mil J - Space	1 - White	Length in 1 Inch Increments	B
		15		6 - 26		2 - Yellow		P
		21		8 - 28		5 - Mil-STD-681 Striped		L
		25		0 - 30		7 - 10 Color Repeat		K
		31						M
		37						S
		51						M1
								S1
								F
								R
Sample Part Number:								
MWD	L	— 9	P	— 6	K	1	— 24	B

* SEE INSIDE BACK COVER FOLD-OUT FOR COMPLETE INFORMATION