


ITEM NO.	PART NUMBER	DESCRIPTION	QTY.	COMPONENT NOTES
1	50-00024	Connector, dc plug, 5.5x2.1xL23 mm, molding style, spring contacts	1	
2	30-00680	Wire, 2C TS, 16 AWG, UL2464, 300V, 80C, 6.1 mm, VW-1, PVC	1	
3	24-00182	Overmold, dc plug, 5.5 mm, Tensility	1	PVC, black



Revision:	Date:	Description:	Prepared:	Notes:	TENSILITY tel 1.541.323.3228 800 877.670.7118 fax 1.541.323.4202 web tensility.com	
A	06/06/2019	Initial release	Verified:	RoHS compliant		
			Dimensions are in millimeters.	Function test: no open, no short circuit, no intermittent		
			Tolerances:	Description:	Size:	Part number:
			X: ± 0.5 mm	Cable, 3050 mm, 5.5x2.1x12 mm 50-00024 dc plug to stripped tinned, 16 AWG, 30-00680 wire	A	10-03330
			X.X: ± 0.3 mm		Scale: 1:1	Sheet 1 of 1
			X.XX: ± 0.05 mm			