



Series
DSXSIZE 16 CRIMP RECEPTACLE CONTACT
WIRE SIZE AWG 16-18-20
COMPLIANT TO M39029/12-150Issue:
Dec. 14, 2015Page
1/1

MATERIAL :

- BODY CONTACT : NICKEL COPPER HEAT TREATED HARDNESS < 200 HV
- BARREL ANNEALED HARDNESS 60-80 HV
- PROTECTIVE SLEEVE : PASSIVATED STAINLESS STEEL AISI 305
- FINISH :
- BODY CONTACT : GOLD PER MIL-G-45204 TYPE I OR II GRADE C OR D CLASS 1 50 MICROINCHES OVER NICKEL PLATE PER QQ-N-290


WIRES ACCOMODATED : AWG 16 - 18 AND 20
INSULATION DIAMETER : .103 (2,60) MAX
STRIP LENGTH : .236 (6)

TOOLING

CRIMPING TOOL : M22520/1-01
SELECTOR POSITION : 6 FOR AWG 16
5 FOR AWG 18
4 FOR AWG 20

POSITIONER : M22520/1-02

DIMENSIONS : mm (inch are given for information only)



Estimated weight : 0.80 g

CREATION

PEN: /

NOM: FALETTI

DATE: Mar. 22, 1985

APPR.: /

Issue	Revisions	Name	Approved
Dec. 14, 15	TDS updated	Moutault	Legendre
Dec. 03, 13	Add M39029/12-148 in the title	Moutault	Dupuis
Aug. 05, 08	Modified position color band	VALGRESY	/
Dec. 15, 04	REDRAWN IN CAD	VALGRESY	GOMBERT

616330EN

RADIAL PROPRIETARY INFORMATION