





PRODUCT NUMBER	PITCH
OQxxA1x000J0G	7.50 mm



RECOMMENDED P.C.B LAYOUT
TOP VIEW

Material:

- Item ③ Male contact pin: Copper Tin plated
- Item ④ Terminal housing: Thermoplastic (UL94V-0)

- Electrical:
- | | | |
|--------------------------|---|---|
| | cULus | TUV |
| ● Voltage rating: | 300V | 750V |
| ● Current rating: | 20A | 15A |
| ● Withstanding Voltage: | 1.6 KV | 6KV |
| ● Operating temperature: | -40°C to +115°C | |
| ● Soldering temperature: | 260°C±5°C/5 Sec | |
| ● Safety Approval: |  |  |

DIMENSION

Dim A	NX7.5
Dim B&C	(N-1)X7.5

N= NUMBER OF POLES

Poles	Tolerance
2P-6P	±0.20
7P-12P	±0.30
13P-16P	±0.40

PART NO.: OQ xx A 1 x 0 00J0 G

No. of poles
02 2 poles
03 3 poles
... ..
16 16 poles

Body Color
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)
9 White(RAL1102)
C Green(RAL6018/U)

RoHS compliant
(lead<4%)
In copper Alloy

mat'l. code				surface	tolerance	projection	product family		
				ASME Y14.5	ASME Y14.5		TERMINAL BLOCK		
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title		
					angles		TERMINAL BLOCK		
					parallel		PLUGGABLE SOCKET,CLOSE TYPE,VERTICAL		
					X'±1°		dwg no		
					dr HANKE FENG 040414		sheet 1 of 1 size		
					enrg HANKE FENG 040414		OQxxA1x000J0G		
					chr SHI JUN 040414		A4		
					appd SHI JUN 040414		type		
							CUSTOMER Drawing		
sheet index	revision	sheet		A					