


BWSM0050644233NG00

Search by :

Part Number

Characteristics

Cross reference



MP



Air Core Inductors - Ultra High Current

Series Pdf

RoHSREACHCoC

Product detail

Structure	Air Core
L(mm) ±	4.94Max.
W(mm) ±	6.34Max.
T(mm) ±	4.18Max.
Size Code (JIS/EIA)	5064/1925
Inductance(nH)	33
Unit	nH
Tolerance(±%)	2
Test Frequency(L)	150MHz,200mV
Q Min	100
Test Frequency(Q)	150MHz,200mV
SRF(MHz)Min	1500
RDC(Ω)Max	0.0048
Irms(mA)Typ	3000



Products

- Power Inductor
- EMI-Common Mode Choke
- EMI-Bead
- RF-Signal Inductor
- RF-Passives/Antennas
- LAN Transformer
- Resistor & Current Sensor

Applications

- Automotive
- Industrial
- Server/DataCenter
- Communication
- Mobile and Tablet
- Computer/Laptop
- Consumer

Design Tools

- Simulation Tool
- Product Search Engine
- E-Catalogue

About Us

- Corporate Overview
- Corporate Milestones
- Core Technology
- Certificates & Awards
- Quality and Social Responsibility

Investor

[Financial Information](#)

[Corporate governance](#)

[Stakeholder Contacts](#)

News

[Media Center](#)

[New Products](#)

[Events](#)

[Product Notices](#)

Contact Us

[Contact Info](#)

[Contact Form](#)

[Join Chilisin](#)

[Terms of Use](#)

[Privacy policy](#)

[Sitemap](#)



Inductor



Resistor



Powder

Copyrights © 2018. Chilisin. All rights reserved.