

Aptiv Connection Systems Catalog

Customer Service

Samples Request

Find by Feature

Browse by Category

Browse by Application

Comparison List (0)

Share

Search

Enter part number or keyword

Search Results (1)

Search Options

1 Result(s): [All] - 12176884

☐ Compare

☐ 12176884 - GT 150 Series Female Sealed Gold Plating Terminal, Cable Range 0.50 - 1.00 mm2

☐ Compare

GT 150 Series Female Sealed Gold Plating Terminal, Cable Range 0.50 - 1.00 mm2



Part # 12176884

[Question about this product?](#)

Attributes

Documents (2)

Part # :	12176884
Description :	GT 150 Series Female Sealed Gold Plating Terminal, Cable Range 0.50 - 1.00 mm2
Product Type :	Terminal
Status :	✓ Active
Blade size [mm] :	1.5
Terminal Family :	GT
Series :	150
Gender :	Female
Sealable :	Sealed
Material :	CuNi3Si1Mg
Weight [g] :	1
Plating :	Gold
Minimum Cable Diameter [mm] :	1.40
Maximum Cable Diameter [mm] :	2.10
Minimum Cable Core Cross Section [mm2] :	0.50
Maximum Cable Core Cross Section [mm2] :	1.00
Temperature Range :	-40 to 125
Voltage Drop :	Less than 10.0
RoHs compliant :	✓ Yes
ELV compliant :	✓ Yes

Certain products listed on this website may be subject to restricted usage or distribution or may not be available. For additional information, please contact your local sales office.

