

6

5

4

3



2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	9/14/11	
A		ADDED SPEC.	6/27/13	



SPECIFICATIONS:

Material:

Insulator: Thermoplastic, rated UL 94V-0

Insulator color: Green

Screw: M2.5, Steel, Zn plated.

Contact: Brass, Tin plated.

Electrical:

Operation voltage: 300 VAC

Current rating: 10 Amps

Mechanical:

Solid wire (AWG): 12-24

Stranded wire (AWG): 12-24

Withstanding Voltage: 1.6KV

Wire strip length: 6-7mm

Temperature Rating:

Operating temperature: -40°C to +115°C

Environmental:

Lead free, RoHS compliant.



Poles: 2 thru 24
A = .197 [5.00] X No. of Positions
B = .197 [5.00] X No. of Spaces

	Tolerance
2-6P	±.006 [0.15]
7-12P	±.008 [0.20]
13-18P	±.012 [0.30]
19-24P	±.016 [0.40]

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

EURO BLOCK, .197" [5.00] PITCH

UNLESS OTHERWISE SPECIFIED			
ALL DIMENSIONS ARE MM [INCHES]			
TOLERANCES: EXCEPT AS NOTED			
INCHES			
X	± .10	ØX	± .10
.XX	± .020	ØXX	± .015
.XXX	± .015	ØXXX	± .010
APPROVALS		DATE	
DRAWN	AY	9/14/11	
CHECKED			
APPROVED			
SIZE	PART NO.	REV.	
X	EB20-XX-C	-	
REF:	S00007T	SCALE:	NTS
		SHEET	1 OF 1

6

5

4

3

2

1