Part Number : 932503087
Product Description : 5.00mm Pitch, Rast 5, PA Polyamide 6/6, 7 Circuits, Coding Key 04C, Latch Positions 1&2 and 5&6, Black, Glow-Wire Capable
Series Number : 93250
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

932503087_sd.pdf

STEP AP242

SOLIDWORKS

Creo

Specifications

PK-93250-001-001.pdf

PS-93250-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Downloaded from Arrow.com.

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	93250
Description	5.00mm Pitch, Rast 5, PA Polyamide 6/6, 7 Circuits, Coding Key 04C, Latch Positions 1&2 and 5&6, Black, Glow-Wire Capable
Application	Power, Wire-to-Board
Product Name	RAST 5
UPC	884982388277

Agency

UL	E29179

Physical

Circuits (maximum)	7
Color - Resin	Black
Flammability	94V-2
Gender	Receptacle
Glow-Wire Capable	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	6.000/g
Number of Rows	1

Downloaded from Arrow.com.

Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	5.00mm
Pitch - Termination Interface	5.00mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +120°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
Appli-Mate RAST 5 Vertical Headers	90858
Appli-Mate RAST 5 Vertical Headers	91999
Appli-Mate RAST 5 Right-Angle Headers	93003

Use with Part(s)

Description	Part Number
High Normal Force Tabs	94518

Downloaded from Arrow.com.