









Product Datasheet

[German](#)[English](#)[Spanish](#)[French](#)[Japanese](#)[Chinese](#)**R282211000****TOOL / CRIMPING TOOL - HEX 2.67-3.25-4.52 (DIES INCLUDED)**

Product Specifications

Part Number	R282211000
Description	TOOL / CRIMPING TOOL - HEX 2.67-3.25-4.52 (DIES INCLUDED)
Series	TOOLING
 <u>Model</u>	OTHERS
Version	STANDARD
Specific features	NONE
Impedance (Ohms)	0
 <u>Max frequency (GHz)</u>	0.0
 <u>Mating system</u>	N/A
 <u>Interface</u>	N/A
 <u>Geometry</u>	N/A
 <u>Cable attachment</u>	N/A
 <u>Panel mounting</u>	N/A
 <u>Cable groups</u>	N/A
 <u>Cable designations</u>	N/A
Body plating	N/A
Temperature range (°C)	N/A
Center contact plating	N/A
Component	N/A
Contact number	N/A
Position	N/A
In series Interface	N/A
Center contact termination	N/A
PCB mounting	N/A
Datasheet	
Assembly Instructions	

[Buy online](#)



[_Catalog Home](#)

The customer is solely responsible for selecting and using the product.
Picture is not contractual, the marking on the product is not the one shown.