



Part Number : [1300970271](#)
Product Description : Dust-Tight Strain Relief
Wide Range Grip, 1-1/2" NPT, Straight Male,
Cable Diameter 30.48-38.10mm (1.200-
1.500"), Approximate Break Strength 453.59kg
(1400 lbs)
Series Number : 130097
Status : Active
Product Category : Cable Grips
Engineering Number : 36516



Documents & Resources

Drawings
[Drawing 1300970271_sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Cable Grips
Series	130097
Description	Dust-Tight Strain Relief Wide Range Grip, 1-1/2" NPT, Straight Male, Cable Diameter 30.48-38.10mm (1.200-1.500"), Approximate Break Strength 453.59kg (1400 lbs)
NEMA Rating	Dust Tight
Product Family	Strain-Relief Cord Grips
Product Name	Dust-Tight
Type	Strain Relief Grip
UPC	78678836516

Agency

CSA	LR32159
UL	E76954

Physical

Approximate Break Strength	453.59kg (1400 lbs)
Bale Length	N/A
Body Style	Straight
Cable Diameter	30.48-38.10mm (1.200-1.500")
Color - Grommet	N/A
Eye Type	N/A
Gender	Male
Insulated	Yes
Material - Body	Zinc Plated Steel
Material - Grip	Galvanized Steel
Mesh Length	0.298m (11.50")
Number of Holes	N/A
O-Ring	N/A
Thread Size	1 1/2" NPT

This document was generated on Sep 26, 2024