

## Han 24M-gg-M40



Image is for illustration purposes only. Please refer to product description.

Part number	19 37 024 0428
Specification	Han 24M-gg-M40
HARTING eCatalogue	<a href="https://harting.com/19370240428">https://harting.com/19370240428</a>

### Identification

Category	Hoods / Housings
Series of hoods/housings	Han <sup>®</sup> M
Type of hood/housing	Hood
Type	High construction

### Version

Size	24 B
Version	Top entry
Number of cable entries	1
Cable entry	1x M40
Locking type	Double locking lever
Field of application	Hoods/housings for rough environments

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65 IP66 IP67
Type rating acc. to UL 50 / UL 50E	4 4X 12



Pushing Performance  
Since 1945

## Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R1 (HL 1-3) R7 (HL 1-3)

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE DNV GL

## Commercial data

Packaging size	1
Net weight	48 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140128897
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466