

6LS1-4C
[\(Home : Products : Switches : MICRO SWITCH™ Limit Switches : MICRO SWITCH™ Medium-Duty Limit Switches : LS \)](#)


Enclosed Switches Series LS: Side Rotary with Yoke Style Lever; Steel Rollers; 1NC 1NO DPDT Snap Action, Maintained, Double Break; 20 mm [0.79 in] conduit; Compact/Non Plug-in

Actual product appearance may vary.

Sales & Service

Distributor Inventory

Overview

Specs

Documentation

Application Notes

Distributor Inventory

Input part number for stock availability

Narrow Your Search**Modify Your Search****Products** Select Option**Technology** Select Option**Industries Served** Select Option

Product Specifications	
Availability	Global
Operating Force (OF)	0,34 N m [3 in lb] max.
Pretravel (PT)	55° max.
Product Type	MICRO SWITCH™ Compact Limit Switches
Actuator	Side Rotary
Lever Type	Yoke Style Roller Lever with Steel Rollers (.75 in dia. x .25 in wide)
Circuitry	1NC 1NO SPDT Snap Action, Maintained, Double Break
Ampere Rating	10 A Ind./0.8 A Res./0.4 Res./0.1 A Res.
Supply Voltage	120 Vac, 240 Vac, 480 Vac/115 Vdc/230 Vdc/550 Vdc
Housing Material	Zinc Die-Cast
Termination Type	20 mm [0.79 in] Conduit
Housing Type	Compact / Non Plug-In
Series Name	LS
Sealing	NEMA 1, 3, 4, 6, 13
Operating Temperature	-29 °C to 71 °C [-20 °F to 160 °F]
Comment	Solder terminals, Two-position maintained
UNSPSC Code	302119
UNSPSC Commodity	302119 Switches and controls and relays
Sealed	Industrial

Product SearchProduct Type: All Product Types New Products OnlyIndustry: All Industries Entire Product CatalogSearch Term: **Search****My Links**

eCOM Login
 Request Access to eCOM
 Rep/AD Portal Login
 Rep/AD Portal Access Request
 Sample Request
 Digital University Login

Literature and Media

Data Sheets
 Videos
 Literature
 Literature Request
 White Papers
 Application Notes

Contacts

Customer Service
 Technical Support
 Global Sales & Service
 Website Feedback

Limitless Microsite
Supplier Microsite

Application Demos



[Terms & Conditions](#)

[Privacy Statement](#)

[Site Map](#)