Part Number : 797582044
Product Description : Pre-Crimped Lead Sabre Female-to-Sabre Female, Tin (Sn) Plating, 300.00mm Length, 16 AWG, Black
Series Number : 79758
Status : Active
Product Category : Power and Signal Cable Assemblies



Documents and Resources

Drawings

797582044_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	79758
Description	Pre-Crimped Lead Sabre Female-to-Sabre Female, Tin (Sn) Plating, 300.00mm Length, 16 AWG, Black
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Sabre Crimp Terminals
Keyword	Pre-Crimped Leads
Product Name	Sabre
UPC	889056821087

Physical

Cable Length	300.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Black
Gender	Female-Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	7.303/g
Packaging Type	Bag
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 1061
Wire Size (AWG)	16

Downloaded from Arrow.com.

Mates With / Use With

Use with Part(s)

Description	Part Number
Sabre Receptacle Crimp Housings	44441

Downloaded from Arrow.com.