

Product Status	Obsolete
	Recommended Alternate Part No. : CLF10040T-330M-D (Interchangeability is not guaranteed.)
	Discontinue Issue Date : May.18, 2017
	Last Purchase Order Date : Mar.29, 2019
	Last Shipment Date : Sep.30, 2019
Applications	Commercial Grade
Feature	Wire WoundWire Wound
	ShieldMagnetic Shield
	Ferrite CoreFerrite Core
Series Type	CLF
Brand	TDK
Environmental Compliance	RoHS REACH Lead Free



Size	
Length(L)	10.00mm ±0.30mm
Width(W)	9.70mm ±0.30mm
Thickness Height	3.80mm ±0.30mm
Recommended Land Pattern (A)	2.50mm Nom.
Recommended Land Pattern (B)	5.60mm Nom.
Recommended Land Pattern (C)	3.20mm Nom.







Electrical Characteristics	
Inductance	33μH ±20% at 100kHz
Rated Current (L Change) [Typ.]	2.2A (10% Down)
Rated Current (L Change) [Max.]	
Rated Current (Temperature Rise) [Typ.]	1.7A (30°C Rise)
Rated Current (Temperature Rise) [Max.]	
DC Resistance [Typ.]	80mΩ
DC Resistance [Max.]	96mΩ
Rated Voltage [Max.]	
Self Resonant Frequency [Min.]	
Self Resonant Frequency [Typ.]	
Q [Min.]	
Q [Typ.]	

Other	
Operating Temp. Range	-40 to 105°C (Including Self-Temp. Rise)


! Images are for reference only and show exemplary products.
! This PDF document was created based on the data listed on the TDK Corporation website.
! All specifications are subject to change without notice.

Soldering Method	Reflow Iron Soldering
AEC-Q200	NO
Packing	Punched (Paper)Taping [330mm Reel]
Package Quantity	800pcs
Weight	1.3g

Characteristic Graphs(This is reference data, and does not guarantee the products characteristics.)



Characteristic Graphs(This is reference data, and does not guarantee the products characteristics.)



Associated Images

