

APC IT Power Distribution Module 3 Pole 5 Wire 32A IEC309 680cm

PDM3532IEC-680

Overview

Presentation	Factory assembled and tested Power Distribution Modules include circuit breaker, power cord, power connection, and circuit monitoring. Auto-detection of modules by the Modular PDU minimizes installation time.
Lead time	Usually Ships within 3 Weeks

Main

Main Input Voltage	400 V 3 phases
Main Output Voltage	230 V 400 V 3 phases
Provided equipment	Installation guide

Physical

Colour	Grey
Height	20.3 cm
Width	43.2 cm
Depth	40.6 cm
Net weight	4.59 kg

Input

Network frequency	50 Hz
Max line current	32 A

Output

Max current draw	32 A
Number of power socket outlets	1 IEC 309 32 A

Conformance

Product certifications	CE
	VDE

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	20.3 cm
Package 1 Width	40.6 cm

Package 1 Length	43.2 cm	
Package 1 Weight	5.5 ka	

Contractual warranty

Warranty 1 year repair or replace



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∅ Environmental footprint

Environmental Disclosure Product Environmental Profile

Use Better

⊗ Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Under investigation

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	Yes

Apr 27, 2025