

[contacts](#)Distributor Inventory

Availability	North America; Asia-Pacific; Latin America
Operating Force (OF)	11,8 N [2.65 lb] max.
Release Force	4,90 N [1.10 lb] max.
Pretravel (PT)	1,5 mm [0.06 in] max.
Overtravel (OT)	3,0 mm [0.118 in] max.
Differential Travel (DT)	0,1 mm [0.004 in] max.
Product Type	MICRO SWITCH™ Miniature Limit Switches
Actuator	Cross Roller Plunger (90° Rotated Plunger)
Lever Type	None
Circuitry	1NC 1NO SPDT Snap Action
Ampere Rating	1 A
Supply Voltage	125 Vac/30 Vdc
Housing Material	Zinc Die-Cast
Termination Type	Cable Gland
Series Name	SL1
Sealing	IP67; NEMA 3, 4, 13
Operating Temperature	-50 °C to 70 °C [-58 °F to 160 °F]
Comment	M3 Terminal screws; 5,8 mm to 9,6 mm outside cable diameter; Gold contacts; Cold and weather resistant; Low current load
Sealed	Industrial
Contact Material	Gold

MICRO SWITCH
Anniversary site