

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20




© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED	24.SEP'14	CH	HG
	B	REVISEC(ECR-19-006223)	23APR2018	TY	YJ



3D VIEW







TABLE 1. 3

CONTACT	PART NO.	WIRE SIZE(SQ)	INSULATION DIAMETER(mm)
.025 TH	2005097-1	0.22	1.05
	2005427-1	0.3~0.5	1.1~1.7
.060	2109006-1	0.22~0.35	1.0~1.5
	2109006-2	0.5~0.75	1.4~1.9
	2109006-3	0.85~1.25	1.8~2.4
.110	1-968880-1	0.35~0.5	1.15~1.6
	1-968849-1	>0.5~1.0	1.4~2.1
	1-968851-1	1.25~2.5	2.2~3.0
	1-968853-1	>2.5~3.0	3.4~3.7
.250	1241402-1	0.5~1.0	1.4~2.1
	1241404-1	>1.0~2.5	2.2~3.0
	1241406-1	>2.5~4.0	3.3~4.5
	1241408-1	4.0~5.0	3.4~4.6

NOTE

1. GENERAL TOLERANCE: ± 0.2 , $\pm 3^\circ$
2. DELIVERY CONDITION
3. APPLICABLE RECEPTACLE CONTACT P/N: SEE TABLE 1
4. SEE THE KEY CODE TABLE
5. APPLICABLE CAP P/N: 2219151



SECTION B-B

KEY CODE TABLE 4

ASS'Y P/N	2219147-2	1-2219147-4
CODE		
	DBL HSG : NATURAL	DBL HSG : BLACK

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED.
	0 PLC $\pm$ 1 PLC $\pm$ 2 PLC $\pm$ 3 PLC $\pm$ 4 PLC $\pm$ ANGLES $\pm$ FINISH N/A
MATERIAL SEE TABLE	

DWN CH CHO	-
CHK KT LIM	-
APVD HG CHO	-
PRODUCT SPEC 108-61235	-
APPLICATION SPEC 411-61022	-
WEIGHT -	-
CUSTOMER DRAWING	



TE Connectivity

NAME -	025/060/110/250 HYB26P PLUG ASS'Y	RESTRICTED TO -
SIZE A3	CAGE CODE 00779	DRAWING NO C-2219147
SCALE 1:1	SHEET 1	OF 1
REV B		