



Pushing Performance
Since 1945

PP-V14-CC-IDC-RJ45-8P-P-M-STR-SHLD



Image is for illustration purposes only. Please refer to product description.

Part number	09 35 220 0401
Specification	PP-V14-CC-IDC-RJ45-8P-P-M-STR-SHLD
HARTING eCatalogue	https://b2b.harting.com/09352200401

Identification

Category	Connectors
Series	Han [®] PushPull (V14)
Element	Connector
Specification	AIDA compliant
	PROFINET
	Multi Feature RJ45
	Straight
Features	Suitable for all PoE versions

Version

Termination method	IDC termination
Shielding	Fully shielded, 360° shielding contact
Number of contacts	8
Coding	RJ45

Technical characteristics

Conductor cross-section	0.12 ... 0.32 mm ² Stranded
	0.12 ... 0.32 mm ² Solid
Conductor cross-section	AWG 26/7 ... AWG 22/7 Stranded
	AWG 24/1 ... AWG 22/1 Solid
Wire outer diameter	0.8 ... 1.6 mm
Transmission characteristics	Cat. 6 _A Class E _A up to 500 MHz



Pushing Performance
Since 1945

Technical characteristics

Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
	5 Gbit/s
	10 Gbit/s
Limiting temperature	-40 ... +85 °C
Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP65
	IP67
Cable diameter	6.5 ... 9.5 mm
Vibration resistance	10-500 Hz, 0.35 mm / 50 m/s², 2h/Achse
	5.72 m/s² acc. to IEC 61373 Category 1 Class B
Shock resistance	50 g / 30 ms, 3 shocks / axis and direction acc. to IEC 61373 Category 1 Class B

Material properties

Surface (contacts)	Au over Ni Mating side
	Sn over Ni Termination side
Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	IEC 60603-7 Mating face
	ISO/IEC 11801
	EN 50173-1
	IEC 61076-3-117 Variant 14
Approvals	DNV GL
PROFINET	Yes

Commercial data

Packaging size	1
----------------	---



Pushing Performance
Since 1945

Commercial data

Net weight	94.37 g
Country of origin	Latvia
European customs tariff number	85366990
GTIN	5713140224278
ETIM	EC002636
eCl@ss	27440114 Rectangular connector (for field assembly)