

★★★★★

0 Reviews

★★★★★

0 Reviews

Need Help?

< Browse All Products

Cat5e / Cat6 / Cat6a

Cat5e

Cat5e TAA Snagless Patch Cable

Loading...

50ft Cat5e Snagless Unshielded (UTP) Ethernet Network Patch Cable (TAA Compliant) - Blue

Use for network adapters, hubs, switches, routers, DSL/cable modems, patch panels and other high performance networking applications.

★★★★★

0 Reviews

Roll over image to zoom in

Product # : 10287

Connector 1 : (1) RJ-45 Male

Connector 2 : (1) RJ-45 Male

Colors :

- Blue

Grey

Black

Lengths :

- 50ft

1ft

3ft

5ft

7ft

10ft

+ show all lengths

160 In Stock & ready to ship!



Add



Need it shipped today?

Place your order before the timer runs out!

08: 02: 33

print share chat

Product Info

★ Customer Reviews

? Questions & Answers

🌐 Distributors

⋮ More Choices

Description

Certifications

Specs

Uses

Product Description

For voice/data/video distribution, this cable will handle bandwidth-intensive applications. Meets all TIA/ANSI Cat5e standards and the stringent TAA compliance requirements for anyone who needs to procure products exclusively manufactured in countries on the Trade Agreement Act list.

Each of the individual pairs is bonded together to help maintain the twist-spacing throughout the line right up to the termination point.

Constructed from high quality cable and a shortened body plug, this design minimizes Near-End Crosstalk (NEXT) levels. Available in a variety of colors to easily color-code your network installation.

WARNING: Cancer and Reproductive Harm www.P65Warnings.ca.gov

Product Certifications



Product Specifications

Color :	Blue
Length :	50.00 Foot
UPC :	757120102878
Warranty :	Lifetime
Vendor :	C2G
Weight :	1.086 LB

For more detailed specifications, please [read this](#).

- Conductor: 4-pair (UTP) 24 AWG stranded copper
- Connector: 50 micron gold-plated RJ45

Electrical Specifications

- Conductor DC Resistance: 89 Ohm/km (maximum)
- Insulation Resistance: 100 Ohm/km (minimum)
- Dielectric Strength: 500 MV/m

Physical Characteristics

- Conductor Type/Size - Bare Copper Stranded, 24 AWG (7/0/2.0)

Insulation

- Material - H-D PE
- Diameter - 0.95 ± 0.05mm
- Colors - Blue/Blue-White, Orange/Orange-White, Green/Green-White, Brown/Brown-White

Jacket

- Material - FR-PVC
- Nominal Thickness - 0.55mm
- Outer Diameter - 5.30mm

Connector

- Material - Polycarbonate
- Hood Material - Molded PVC
- Contact Material - Copper alloy plated with gold-50μ
- Number of contacts - Eight

Other Specifications

- Approvals - RoHS Compliant, Verified to EIA/TIA 568B.2
- Wired - TSB 568B (AT&T 258A)
- Package Type - Polybag

Product Uses

- 1000 BASE-T; 100 BASE-T; 10 BASE-T (IEEE 802.3)
- 4/16 Mbps Token Ring (IEEE 802.5); 100 VG-AnyLAN
- 100 Mbps TP-PMD (ANSI X3T9.5); 55/155 Mbps ATM

Info

[About Us](#)

[Order History](#)

[Where To Buy](#)

[More](#) ▾

Service

[Contact Us](#)

[OEM Solutions](#)

[Tech Support](#)

[More](#) ▾

Resources

[Connector Guides](#)

[ConnectXpress](#)

[Drivers & Manuals](#)

[More](#) ▾

Have A Question?

Get help with [Chat](#)

Call C2G **800.506.9607**



United States | [Europe +](#)

Copyright © 2019 C2G. All Rights Reserved

